

KERN DS 36K0.2L

Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications



Display

Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction

Dimension housing (W×D×H)	225×115×60 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×125 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Level indicator	✓
Levelling feet adjustable	✓
Stand height	450 mm
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Display device cable length	2,5 m

Functions

PreTare function	✓
Sum memory function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	360.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	36 kg
Readability [d]	0,0002 kg
Reproducibility	0,0002 kg
Linearity	± 0,0006 kg
Resolution	180.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (F1); 10 kg (F1)
Possible calibration points	10 kg; 15 kg; 20 kg; 30 kg; 36 kg
Stabilization time	3 s
Eccentric loading at 1/3 [Max]	0,001 kg
Construction type of the scale	Single-range balance

Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa
-------	---

Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g
Default unit	kg

KERN DS 36K0.2L



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP
	WiFi (optional)
compatible with EasyTouch	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	600×510×230 mm
Shipping method	Parcel service
Net weight approx.	19 kg
Gross weight approx.	22 kg
Shipping weight	20,5 kg
Shipping volume weight	14,1 kg

Product information

GTIN/EAN number	4045761357020
Trade number	84238220
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------