

# SAUTER TE 1250-0.1FN

# KERN

Ergonomic design and external measuring head for highest ease of use



## Category

Brand	Sauter
Product category	Coating thickness measuring device
Product group	Digital coating thickness gauge
Product family	TE

## Measuring System

Offset accur (% of [Max])	1%
Measuring range coating thickness [d] (µm)	100 µm; 1250 µm
Readability coating thickness [d] (µm)	0,1 µm; 1 µm
Coating thickness gauge sensor type	FE NFE
Test object thickness coating	Non-magnetic coatings on iron, steel, Type F Coatings on non-magnetic metals, type N
Minimum thickness base material	300 µm
Smallest sample, flat [radius]	6 mm
Smallest sample, convex [radius]	1,5 mm
Smallest sample, concave [radius]	50 mm
Sensor placement position	external
Units	µm inch (mil)
Tolerance (% of [Max])	3%

## Display

Display type	LCD
Display digit height	10 mm

## Construction

Dimension (W×D×H)	131×65×28 mm
Dimension housing (W×D×H)	131×65×28 mm
Dimensions completely mounted (W×D×H)	131×65×28 mm
Material housing	plastic
Cable length	1 m

## Functions

Increase in measurement accuracy possible	✓
---	---

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AAA
Battery operating time	50 h
Battery capacity	1.100 mAh
Battery voltage	1,5 V

## Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Storage temperature [Min]	0 °C
Storage temperature [Max]	50 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for factory calibration	961-112
--	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×215×73 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,75 kg
Shipping weight	0,8 kg


# SAUTER TE 1250-0.1FN



Ergonomic design and external measuring head for highest ease of use

## Pictograms

### STANDARD



### OPTION

