

KERN EFC 60K-3L

Platform scale with integrated rechargeable battery pack, a bright LED display and a column for greatest ease of use



Display type	LED segments
Display backlight	no
Display screen size	165×64 mm
Display segments	6
Display digit height - smallest digit	52 mm
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction

Dimension display device (W×D×H)	252×162×57 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	steel, lacquered
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	600 mm
Stand rotatable	✓
Stand inclinable	✓
Display device cable length	3 m
Load cells - number	1

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	24.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	2,5 g
Smallest piece weight when piece counting - normal conditions	25 g
Reference quantity	n (any number of pieces)
IP protection - display	no IP protection

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	EFC

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,005 kg
Reproducibility	0,005 kg
Linearity	± 0,015 kg
Resolution	12.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (F2)
Possible calibration points	6 kg; 12 kg; 15 kg; 20 kg; 30 kg; 40 kg; 60 kg
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,025 kg
Construction type of the scale	Single-range balance
Units	kg lb PCS
Load cell connection	4-wire
Maximum creep (15 minutes)	20 g
Maximum creep (30 minutes)	40 g
Default unit	kg
Loadcell type	aluminium IP65 silicone-coated

Display

Display type	LED segments
--------------	--------------

KERN EFC 60K-3L

KERN

Platform scale with integrated rechargeable battery pack, a bright LED display and a column for greatest ease of use

Tare function	manual (single & multi)
Number of keys for operation	7

Interface	
Interfaces	RS-232 standard

Power Supply	
Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK
Plug-in power supply / adapter for countries - optional	EURO UK
Input voltage power supply / power [Max]	100 - 240 V 50/60 Hz 0.5 A
Input voltage device / power [Max]	5 V, 1 A

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 10,5 mm
--------------------------------	--

Battery / accumulator type	Li-Ion
Battery capacity	4.000 mAh
Battery voltage	3,7 V
Battery - Individual weight	93 g
Battery capacity (Wh)	14,8 Wh
Battery - Tests passed UN 38.3	✓
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	50 h

Battery/Accu connected	fixed electrical connection, no leakage current (insulated)
------------------------	---

Environmental conditions	
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval	
CE mark	✓

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping	
Delivery time	1 d
Dimensions packaging (W×D×H)	930×550×220 mm
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	13 kg
Shipping weight	22,5 kg
Shipping volume weight	22,5 kg

Product information	
GTIN/EAN number	4045761252653
Trade number	84238220
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

