

KERN EHA 3000-1

The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries, and for teaching



Display	
Display type	LCD
Display backlight	✓
Display screen size	75×32 mm
Display segments	6
Display digit height	22 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	225×160×50 mm
Dimensions weighing surface (W×D)	120×120 mm
Dimensions weighing surface	120×120 mm
Dimensions weighing platform (W×D×H)	120×120×7 mm
Material housing	ABS plastic
Material weighing plate	stainless steel
Material platform	Plastics
Material display housing	Plastics
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓

Functions	
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
Tare function	manual (multi)
Number of keys for operation	5

Power Supply	
Supplied power supply	Power supply & battery function (battery not included)
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Input voltage power supply / power [Max]	100 - 240 V

Category	
Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EHA

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	3000 g
Readability [d]	0,1 g
Reproducibility	0,3 g
Linearity	± 0,3 g
Resolution	30.000
Tare range	3000 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1 kg (F2); 3 kg (F2)
Possible calibration points	1 kg; 3 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,5 g
Maximum creep (15 minutes)	400 mg
Maximum creep (30 minutes)	800 mg
Default unit	g
Units	g gn dwt ct oz

KERN EHA 3000-1

The compact all-round model with robust stainless steel weighing plate for use in laboratories, industries, and for teaching

Input voltage device / power [Max]	9 V, 600 mA
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery connection	Battery insert
Battery operating time	70 h

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	245×204×76 mm
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	0,75 kg
Shipping weight	0,8 kg

Pictograms

STANDARD



OPTION

