


Product brochure

08.08.2026

KERN EWJ 600-2M

High-quality precision balance with automatic internal adjustment, verification optional

ENGLISH




CONTACT

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen
Germany

+49 7433 9933-0
info@kern-sohn.com
www.kern-sohn.com

APPLICATION EXAMPLE



FEATURES

- Weighing with tolerance range (checkweighing): a visual and audible signal helps with portioning, dispensing or grading
- Standardised, convenient KERN concept of operation: All primary functions have their own key on the keypad
- Automatic internal adjustment, time-controlled every 2 h, guarantees high degree of accuracy and makes the balance independent of its location
- Capacity display: A bargraph display lights up to show how much of the weighing range is still available
- USB data interface for transferring weighing data to the PC, printer etc.
- Draught shield standard, weighing space W×D×H 134×128×80 mm, removable
- Protective working cover included with delivery

TECHNICAL DATA

- Large LCD display, digit height 21 mm
- Dimensions weighing surface, stainless steel
Ø 120 mm
W×D
- Overall dimensions (without draught shield) W×D×H 220×340×90 mm
- Overall dimensions (incl. draught shield) W×D×H 220×340×180 mm
- Permissible ambient temperature 10 °C/35 °C

MAIN SCOPE OF APPLICATIONS


- Jewellery and gold trade
- Quality control
- Laboratory applications
- Dental laboratories
- Plastics technology

PLEASE NOTE FOR YOUR ORDER

- For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order, the initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification
- According to the requirements of the EU Directive and the German Weights and Measures Act, scales in open sales outlets must not have an auxiliary display device. (Scales for the intended use 'open points of sale' must have a readability of $e=d$).

PICTOGRAMS

Standard



Option



Factory



MODEL OVERVIEW

Model	Weighing capacity [Max]	Readability [d]	Verification value [e]	Minimal load [Min]	Reproducibility	Linearity	Dimensions weighing surface
EWJ 300-3	300 g	0,001 g			0,003 g	$\pm 0,005$ g	80 mm
EWJ 300-3H	300 g	0,001 g			0,003 g	$\pm 0,005$ g	80 mm
EWJ 600-2M	600 g	0,01 g	0,1 g	0,5 g	0,01 g	$\pm 0,03$ g	120 mm
EWJ 600-2SM	600 g	0,01 g	0,1 g	0,5 g	0,01 g	$\pm 0,03$ g	120 mm
EWJ 600-3	600 g	0,001 g			0,003 g	$\pm 0,005$ g	120 mm
EWJ 3000-2	3000 g	0,01 g			0,03 g	$\pm 0,05$ g	135 mm
EWJ 6000-1M	6000 g	0,1 g	1 g	5 g	0,1 g	$\pm 0,3$ g	155×145 mm
EWJ 6000-1SM	6000 g	0,1 g	1 g	5 g	0,1 g	$\pm 0,3$ g	155×145 mm
EWJ 6000-2	6000 g	0,01 g			0,07 g	$\pm 0,1$ g	155×145 mm

ACCESSORIES

Model	Description
AFH 13	Converter RS232 to USB AFH 13
CFS-A01	RS232 interface cable CFS-A01
EWJ-A04	Protective working cover EWJ-A04
EWJ-A04S05	Protective working cover EWJ-A04S05, scope of delivery: 5 items

Model	Description
EWJ-A06	Rechargeable battery pack EWJ-A06 (Li-Ion, 7,4 V, 2.600 mAh)
PFB-A10	Bluetooth Data Interface KERN PFB-A10, for wireless data transfer to PC or tablets, supports Bluetooth 2.0 and 4.0 (must be ordered at purchase)
YKA-11	Power adapter YKA-11 (12 V, 500 mA 100 - 240 V~ 50/60 Hz 190 mA EURO, AUS, UK, US, CH)
YKC-01	Thermal printer YKC-01
YKG-01	Dot Matrix Printer YKG-01
YKH-01	Thermal printer YKH-01
YKI-02	RS232-Bluetooth-Adapter YKI-02
YKI-10	RS232-Ethernet adapter YKI-10 (RS-232 standard, Ethernet, RS-485)
YKI-11	RS232-Ethernet adapter YKI-11 (Ethernet, RS-232 standard - 2x)
YKI-12	RS232-WiFi adapter YKI-12
YKT-01	Needle printer YKT-01
YPS-03	Antivibration table YPS-03
YPS-04	Anti-vibration plate KERN YPS-04 (400×450×60 mm, 30 kg)
YPS-05	Anti-vibration plate KERN YPS-05 (565×450×60 mm, 42 kg)

SOFTWARE

Model	Description
SCD-4.0-DL	Software SCD-4.0-DL (Scope of supplies: Download link for 1 license)
SCD-4.0-DLS05	Software SCD-4.0-DLS05 (Scope of supplies: Download link for 5 licenses)
SCD-4.0-PRO-DL	Software SCD-4.0-PRO-DL (Scope of supplies: Download link for 1 license)
SCD-4.0-PRO-DL-AS05	Software SCD-4.0-PRO-DL-AS05 (Scope of supplies: Download link for 5 licenses)

SERVICES

Model	Description
963-127	DAkkS calibration certificate 963-127
965-216	Verification / Conformity assessment according to NAWI (2014/31/EU) 965-216
969-517	Confirmation of the manufacturer's specification (only in combination with DAkkS calibration certificate) 969-517
970-017	Warranty extension (+3 years) 970-017

KERN Pictogram Overview

	Internal adjustment: Adjusting accuracy using internal adjustment weight
	Data interface RS-232: For connection to printers, PCs or other peripheral devices for data transfer over longer distances. Network in bus topology possible
	Data Interface USB: For connection to printers, PCs or other peripheral devices
	KERN Communication Protocol (KCP): a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems
	Piece counting: Reference quantities selectable. Display can be switched from piece to weight
	Net total: The weight values of the recipe ingredients can be added up and the total weight of the recipe printed out
	Percentage determination: determining the deviation in % from the target value (100 %)
	Measuring with tolerance range (checkweighing): Upper and lower limit values can be programmed, e.g. for sorting, portioning or for measuring coatings or material thicknesses. The process is supported by an acoustic and/or optical signal
	Units can be switched to e.g. non-metric units
	Hold function: When the weighing conditions are unstable, a stable weight is calculated as an average value
	Universal plug-in power supply: With universal input and optional input socket adapters for EU, CH, GB or EU, CH, GB, US or EU, CH, GB, US, AUS
	Weighing principle Strain gauges: Electrical resistor on an elastic deforming body
	Package shipment by courier service: The duration of internal product provision is one day
	Rechargeable battery pack: Rechargeable set
	Accredited calibration (DKD): The duration of the accredited calibration is 3 working days
	Data interface Bluetooth: For connection to printers, PCs or other peripheral devices
	Conformity assessment: The duration of the conformity assessment is 3 working days