


# KERN EWJ 6000-2

High-quality precision balance with automatic internal adjustment



Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	EWJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6000 g
Readability [d]	0,01 g
Reproducibility	0,03 g
Linearity	± 0,05 g
USP Minimum weight of sample (k = 2, U = 0.1%)	60 g
Resolution	600.000
Adjustment options	Internal calibration (automatic)
Recommended adjusting weight	6 kg (E2)
Possible calibration points	2 kg; 4 kg; 6 kg
Automatic adjustment - Standard time interval	2 h
Stabilization time	6 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,04 g
Maximum creep (15 minutes)	100 mg
Maximum creep (30 minutes)	200 mg
Default unit	g
Units	kg
	g
	gn
	dwt
	tl (Tw)

Loadcell type	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
	ffa
	tol
	m
	aluminium IP65 silicone-coated

Display	
Display type	LCD
Display backlight	✓
Display screen size	129 x 27
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	220×340×105 mm
Dimensions weighing surface (W×D)	155×145 mm
Dimensions weighing surface	155×145 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions	
PreTare function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Capacity - Display	✓
Counting function	✓
Counting resolution (laboratory conditions)	600.000
Counting reference weight can be entered	✓

# KERN EWJ 6000-2

# KERN

High-quality precision balance with automatic internal adjustment

Smallest piece weight when piece counting - laboratory conditions	10 mg
Smallest piece weight when piece counting - normal conditions	100 mg
Reference quantity	5, 10, 20, 50, free, Input
Hold function	✓
IP protection - display	no IP protection
IP protection - load cell	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Tare function	manual (multi)
Number of keys for operation	7

## Interface

Interfaces	RS-232 standard
	Bluetooth BTC (v2.0) (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
	USB-Device

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Battery / accumulator type	Pb
Battery connection	2-pole tub connector
Rechargeable battery operating time - backlight on	32 h
Rechargeable battery operating time - backlight off	57 h
Rechargeable battery charging time	6,5 h
Rechargeable battery optional	Rchrg. battery optional - intern

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %

## Approval

CE mark	✓
---------	---

## Services (optional)


Article number for DAkkS calibration	963-104
Article number for certificate of conformity	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	410×295×275 mm
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	4,6 kg
Shipping weight	6,7 kg

## Pictograms

### STANDARD



### OPTION



### FACTORY

