

# KERN FCB 12K-4

Checkweighing and portioning scale with up to three interfaces



Loadcell type	aluminium IP65 silicone-coated
---------------	--------------------------------

Display	
Display type	LCD
Display backlight	✓
Display screen size	120×38 mm
Display digit height	25 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	322×267×91 mm
Dimensions completely mounted (W×D×H)	325×270×105 mm
Dimensions weighing surface (W×D)	252×225 mm
Dimensions weighing surface	252×225 mm
Material housing	plastic
Material weighing plate	stainless steel
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,4 Nm

Functions	
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	120.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 20, 50, free, Input
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	IP65

Category	
Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	FCB

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	12 kg
Readability [d]	0,0001 kg
Reproducibility	0,0001 kg
Linearity	± 0,0003 kg
Resolution	120.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	12 kg (F2)
Possible calibration points	2 kg; 5 kg; 10 kg; 12 kg
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,0005 kg
Construction type of the scale	Single-range balance
Units	kg g gn dwt ct lb oz ffa PCS %
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	kg

# KERN FCB 12K-4



Checkweighing and portioning scale with up to three interfaces

Auto-off interval(s) in battery mode/rechargeable battery mode	2 min
	1 min
	30 min
	60 min
	30 sec

Tare function	manual (multi)
Number of keys for operation	6

## Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP WiFi (optional)

compatible with EasyTouch	✓
---------------------------	---

## Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Power supply type	Power adapter
-------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH

Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
--	------------------------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	5,9V, 1A
------------------------------------	----------

Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
--------------------------------	--

Battery / accumulator type	Li-Ion
----------------------------	--------

Battery operating time	20 h
------------------------	------

Rechargeable battery operating time - backlight on	24 h
--	------

Rechargeable battery operating time - backlight off	48 h
---	------

Rechargeable battery charging time	8 h
------------------------------------	-----

Rechargeable battery optional	Rchrg. battery optional
-------------------------------	-------------------------

## Environmental conditions

Ambient temperature [Min]	0 °C
---------------------------	------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration	963-128
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

## Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	395×335×200 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	3,8 kg
--------------------	--------

Gross weight approx.	4,2 kg
----------------------	--------

Shipping weight	5,3 kg
-----------------	--------

Shipping volume weight	5,3 kg
------------------------	--------

## Product information

GTIN/EAN number	4045761243477
-----------------	---------------

Trade number	84238129
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

## Pictograms

### STANDARD



### OPTION

