

SAUTER FE 5

KERN

Digital force gauge with pass-fail function for tensile and compressive force measurements



Date of creation: 30.06.2026

Category	
Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge
Product family	FE

Measuring System	
Directions of force	tension compression
Measuring range force [Max] (N)	5 N
Readability force [d] (N)	0,002 N
Measuring head measuring frequency	1000 Hz
Overload protection (% of [Max])	150%
Tolerance (% of [Max])	0,3%
Default unit	N

Display	
Display type	LCD
Display digit height	8,5 mm
Screen reversible	✓

Construction	
Dimension housing (W×D×H)	71×31×180 mm
Dimensions completely mounted (W×D×H)	71×31×180 mm
Material housing	ABS plastic
Mounting - force application	External thread M6
Load support (tensile force)	Hook

Functions	
Limit-setting function	✓
Peak function	✓

Power Supply	
Supplied power supply	Accu & Power supply
Power supply type	USB including power supply
Input voltage power supply / power [Max]	100 V - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A
Power socket for mains adapter	USB C
Battery / accumulator type	NiMH
Battery capacity	750 mAh
Battery voltage	4,8 V
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	10 h
Rechargeable battery charging time	8 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions	
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval	
CE mark	✓

Services (optional)	
Article number for DAkKS calibration (tensile force)	963-1610
Article number for DAkKS calibration (compressive force)	963-2610
Article number for DAkKS calibration (tensile force/ compressive force)	963-3610
Article number for factory calibration (tensile force)	961-1610
Article number for factory calibration (compressive force)	961-2610

SAUTER FE 5



Digital force gauge with pass-fail function for tensile and compressive force measurements

Article number for factory calibration (tensile force/ compressive force) 961-3610

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	263×230×75 mm
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,95 kg
Shipping weight	0,914 kg
Shipping volume weight	0,9 kg

Product information

GTIN/EAN number	4045761505551
Trade number	90248000
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

