



Compact stainless steel bench scale with special checkweighing display for even more efficient working, verification optional

Features

- **1** Innovative weighing with tolerance range: The colour of the display changes depending on the weight (too light/ok/too heavy) and is an aid to help with portioning, dosing and grading
- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- **2** Ideal for the increased hygienic requirements in the food industries
- Thanks to battery operation, compact, light-weight construction, it is suitable for the use in several locations (kitchens, sales offices, cafeterias, food industry laboratories, etc.)
- Your support in a HACCP-compliant quality system

- Protection against dust and water splashes IP65 (only when using battery)
- Increased protection against humidity through waterproof silicone sealing of the load cell, electronics and soldering joints
- Secure and non-slip positioning with rubber feet
- Mains adapter included with the delivery
- Protective working cover included with delivery

Technical data

- Large backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, WxD 248x198 mm
- Overall dimensions WxDxH 256x285x100 mm
- Battery operation, 4x1.5 V AA standard, operating time up to 48 h. AUTO-OFF function to preserve the battery
- Net weight approx. 3,8 kg
- Permissible ambient temperature 0 °C/40 °C

Accessories

- **3** Protective working cover, scope of delivery 5 items, KERN FOB-A13S05
- **4** Tare pan made from stainless steel, ideal for weighing loose small parts as well as fruits, vegetables, etc., overall dimensions WxDxH 400x300x45 mm, KERN RFS-A02

STANDARD



OPTION



FACTORY



Note: Official verification is mandatory for commercial trade

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Options	
					Verification	DAkkS Calibr. Certificate
KERN						DAkkS
					KERN	KERN
FOB 1K-4LM	1,5	0,5	0,5	10	965-227	963-127
FOB 3K-3LM	3	1	1	20	965-227	963-127
FOB 6K-3LM	6	2	2	40	965-228	963-128
FOB 10K-3LM	15	5	5	100	965-228	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.