

# KERN IFB 6K-4S

High-resolution industrial scale in heavy version



## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IFB

## Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	6 kg
Readability [d]	0,0002 kg
Reproducibility	0,0002 kg
Linearity	± 0,0006 kg
Resolution	30.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (F2)
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,001 kg
Load cell connection	4-wire
Construction type of the scale	Single-range balance

Units	kg
	g
	lb
	Hj, tj
	lb:oz

Maximum creep (15 minutes)	800 mg
Maximum creep (30 minutes)	1,6 g
Default unit	kg

Loadcell type	aluminium IP65 silicone-coated
---------------	--------------------------------

## Display

Display type	LCD
Display backlight	✓
Display segments	5 + 1/2
Display digit height	52 mm
Languages of the user interface	Symbol language

## Construction

Dimensions completely mounted (W×D×H)	230×230×360 mm
Dimension display device (W×D×H)	250×160×58 mm
Dimensions weighing surface (W×D)	230×230 mm
Dimensions weighing surface	230×230 mm
Dimensions weighing platform (W×D×H)	230×230×106 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	3300 mm
Stand inclinable	✓
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Display device cable length	3 m
Allowed cable length display device [Max]	3 m
Load cells - number	1

## Functions

Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	10, 20, 50, 100, 200

# KERN IFB 6K-4S



High-resolution industrial scale in heavy version

IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	off 5 min 15 min
Auto-off interval(s) in mains power mode	off 5 min 15 min
Tare function	manual (single & multi)
Number of keys for operation	7

## Interface

Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
------------	--

## Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,5 mm, long 9,5 mm
Battery / accumulator type	Pb
Battery	no battery
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Rechargeable battery charging time	12 h
Rechargeable battery optional	Rchrg. battery optional

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	494×341×227 mm
Shipping method	Parcel service
Net weight approx.	4,6 kg
Gross weight approx.	7 kg
Shipping weight	7,6 kg

## Product information

GTIN/EAN number	4045761244030
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION



### FACTORY

