

# KERN IFC 150K20DLM

Robust industrial scales with up to three interfaces, with optional verification



## Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

## Construction

Dimension display device (W×D×H)	220×150×66,5 mm
Dimensions weighing surface (W×D)	650×500 mm
Dimensions weighing surface	650×500 mm
Dimensions weighing platform (W×D×H)	650×500×139 mm
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1

## Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	7.500

## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IFC

## Measuring System

Weighing system	Strain gauge
Number of weighing ranges	2
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,02 kg; 0,05 kg
Minimum weight [Min] (verifiable)	0,4 kg; 1 kg
Resolution	3.000, 3.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	3 s
Eccentric loading at 1/3 [Max]	0,02 kg; 0,05 kg
Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Units	kg g ffa PCS %
Units (if device is conformity assessed)	kg g
Load cell connection	6-wire
Default unit	kg
Loadcell type	aluminium IP65 silicone-coated

# KERN IFC 150K20DLM



Robust industrial scales with up to three interfaces, with optional verification

Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	20 g
Smallest piece weight when piece counting - normal conditions	200 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	7

## Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
Interfaces	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional)
	analogue (4 - 20 mA) (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP
	WiFi (optional)
compatible with EasyTouch	✓

## Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Battery / accumulator type	Li-Ion
Battery	3 V CR2032
Battery capacity	210 mAh
Battery voltage	3 V
Battery - Number of cells	1
Battery - Individual weight	3,2 g
Battery - Total weight	3,2 g
Battery - Construction	Individual cells
Battery capacity (Wh)	0,66 Wh
Battery - Lithium content	64 mg
Battery - Tests passed UN 38.3	✓
Rechargeable battery	3,7 V, 3200mAh
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

## Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,02 kg; 0,05 kg

## Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

# KERN IFC 150K20DLM



Robust industrial scales with up to three interfaces, with optional verification

Article number for certificate of conformity 969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	675×1045×250 mm
Shipping method	Parcel service
Net weight approx.	18 kg
Gross weight approx.	22 kg
Shipping weight	35,3 kg
Shipping volume weight	35,3 kg

## Product information

GTIN/EAN number	4045761475656
Trade number	84238220
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION



### FACTORY

