

SAUTER LL 600

Precise mini laser rangefinder

KERN



Date of creation: 30.06.2026

Category

Brand	Sauter
Product category	Length measurement
Product group	Length measurement instrument
Product family	LL

Measuring System

Measuring range length [Max]	60 m
Tolerance	2 mm
Measuring range length [Min]	5 cm
Division	1 mm

Display

Display type	LCD graphic
--------------	-------------

Construction

Dimensions completely mounted (W×D×H)	87×37×20 mm
Material housing	aluminium
Material display housing	aluminium
Measurement alignment	vertical/horizontal
Laser power	0,001 W
Laser class	2

Functions

Memory function	✓
-----------------	---

Power Supply

Supplied power supply	Accu
Battery / accumulator type	Li-Ion

Battery capacity (Wh)	0,37 Wh
Rechargeable battery operating time - backlight off	8 h
Rechargeable battery charging time	5 h
Battery/Accu connected	fixed electrical connection, not insulated

Services (optional)

Article number for DAkkS calibration	963-148
Article number for factory calibration	961-148

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	145×83×45 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	404576 1495586
Trade number	90318080
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

