

KERN TN 230-0.01US

KERN

Portable measuring device for ultrasonic material thickness testing



Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TN-US

Measuring System

Material thickness pulse-echo [Min] (mm)	1,2 mm
Material thickness pulse-echo [Max] (mm)	230 mm
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	10 mm
Measuring head measuring frequency	5 MHz
Units	mm inch
Internal data memory: Number of individual values	100
Internal data memory: Number of value groups	20
Tolerance (% of [Max])	0,5%

Display

Display type	LCD
Display digit height	14 mm

Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material housing	plastic
Cable length	0,9 m

Interface

Interfaces	USB-Device
------------	------------

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery operating time	100 h
Battery capacity	3.000 mAh
Battery voltage	1,5 V

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-113
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	315×245×83 mm
Net weight	0,22 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	1,4 kg
Shipping weight	1,38 kg


KERN TN 230-0.01US

Portable measuring device for ultrasonic material thickness testing



Pictograms

STANDARD



OPTION

