

# KERN TN 80-0.1US

**KERN**

Portable measuring device for ultrasonic material thickness testing



## Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material housing	plastic
Cable length	0,9 m

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery operating time	100 h
Battery capacity	3.000 mAh
Battery voltage	1,5 V

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for factory calibration	961-113
--	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	315×245×85 mm
Net weight	0,25 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	1,4 kg
Shipping weight	1,37 kg

## Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TN-US

## Measuring System

Material thickness pulse-echo [Min] (mm)	0,75 mm
Material thickness pulse-echo [Max] (mm)	80 mm
Readability material thickness [d] (mm)	0,1 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	6 mm
Measuring head measuring frequency	7 MHz
Units	mm inch
Internal data memory: Number of individual values	100
Internal data memory: Number of value groups	20
Tolerance (% of [Max])	0,5%

## Display

Display type	LCD
Display digit height	14 mm

# KERN TN 80-0.1US

Portable measuring device for ultrasonic material thickness testing



## Pictograms

### STANDARD

---



### OPTION

---

