

# KERN OBN 159

Professionalism and versatility united in one microscope – with Koehler illumination for demanding applications



## Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBN-15

## Construction

Dimension (WxDxH)	390x200x400 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Siedentopf
Light distribution	0:100 80:20

Contrasting methods	Bright field
	Darkfield (optional)
	Phase contrast
	Polarisation (optional)
	Fluorescent (optinal)

Standard objectives	4x
	PH 10x
	PH 20x
	PH 40x
	PH 100x

Lens quality	Infinity Plan
Nosepiece screw-in locations	5
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

## Ocular

Ocular type	Eyepiece HWF 10x / Ø 20mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular diameter	23,2 mm

## Objective

Objectives - Details	PH-Objective Infinity Plan 10x / 0,25 anti-fungus
	PH-Objective Infinity Plan 100x / 1,25 oil, anti-fungus
	PH-Objective Infinity Plan 20x / 0,45 spring, anti-fungus
	Objective Infinity Plan 4x / 0,11 anti-fungus
	PH-Objective Infinity Plan 40x / 0,65 spring, anti-fungus

Objectives magnifications	4x / 10x / 20x / 40x / 100x
---------------------------	-----------------------------

## Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Koehler illumination	✓
Filter possible	✓
Phase-contrast unit	Quintuple condenser wheel
Aperture diaphragm	✓
Field diaphragm	✓

## Focussing

Field of view [Min]	0,2 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

# KERN OBN 159

# KERN

Professionalism and versatility united in one microscope – with Koehler illumination for demanding applications

## Condensor

Condensor type	PH universal rotary condenser
----------------	-------------------------------

## Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	535×370×270 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	11 kg
Shipping weight	11 kg

## Product information

GTIN/EAN number	4045761267824
Trade number	90118000
REACH classification	no prohibited substances

## Pictograms

### STANDARD



### OPTION

