

KERN OPO 185



The flexible and powerful polarising microscope for all professional applications with reflected and transmitted light



Date of creation: 30.08.2026

Category	
Brand	Optics
Product category	Microscope
Product group	Polarising microscope
Product family	OPO-1
Construction	
Dimension (W×D×H)	519×211×400 mm
Optical system	Infinity
Tube type	Trinocular
Tube angle of inclination	30°
Tube type	Siedentopf
Light distribution	20:80 100:0
Contrasting methods	Bright field Polarisation
Standard objectives	4× 10× 20× 40× 50×
Nosepiece screw-in locations	5
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Supported camera types	Microscope Camera

Ocular	
Ocular type	Eyepiece HWF 10x / Ø 20mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	22 mm
Ocular diameter	30 mm

Objective	
Objectives - Details	Objective Infinity Plan 10x / 0,25 non-stress, anti-fungus Objective Infinity Plan 20x / 0,45 spring, non-stress, anti-fungus Objective Infinity Plan 4x / 0,11 non-stress, anti-fungus Objective Infinity Plan 40x / 0,65 spring, non-stress, anti-fungus Objective Infinity Plan Semi Apochromatic 50x / ... non-stress, LWD
Objectives magnifications	4 x / 10 x / 20 x / 40 x / 50 x

Illumination	
Illuminance	Reflected light Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	5 W
Illumination intensity transmitted light	5 W
Illumination dimmable	Incident light + Transmitted light, separate
Koehler illumination	✓
Filter possible	✓
Field diaphragm	✓

Microscope table	
Pitch Rotary axis	1°; 6'

KERN OPO 185



The flexible and powerful polarising microscope for all professional applications with reflected and transmitted light

Focussing

Field of view [Min]	0,4 mm
Field of view [Max]	5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Polarisation

Lambda slip slot	✓
------------------	---

Condensor

Condensor type	Abbe
Condenser - Mounting	Swing-Out
Condenser - Aperture	0,9 / 1,25
Aperture diaphragm	✓

Camera

Camera - Adapter type	C-Mount
-----------------------	---------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	5 V, 1 A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,5 mm, long 10 mm

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	520×470×430 mm
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	15 kg
Shipping weight	21 kg
Shipping volume weight	21 kg

Product information

GTIN/EAN number	4045761490055
Trade number	90118000
Warranty Time	36 mon
REACH classification	no prohibited substances

Pictograms

STANDARD

