

# KERN PCB 10000-1

The standard in the laboratory, ideal for a wide range of applications for Industry 4.0



tl (Singap, Malays)  
ct  
mo  
lb  
oz  
ffa  
m

Display	
Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	163×245×65 mm
Dimensions weighing surface (W×D)	150×170 mm
Dimensions weighing surface	150×170 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	Plastics
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,4 Nm

Functions	
PreTare function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Hook (included in delivery)
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	50.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCB

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10 kg
Readability [d]	0,0001 kg
Reproducibility	0,0001 kg
Linearity	± 0,0003 kg
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Resolution	100.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F1)
Possible calibration points	2 kg; 5 kg; 10 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0004 kg
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	kg

	kg
	g
	gn
Units	dwt
	tl (Tw)
	tl (HK)
	ozt

# KERN PCB 10000-1



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0

Reference quantity	5, 10, 20, 50, free, Input
IP protection - display	no IP protection
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

## Interface

Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
EasyTouch (ET) - Compatibility	vollständig

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Battery / accumulator type	Li-Ion
Battery	4×1.5 V AA
Battery connection	Battery insert
Battery operating time	20 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	235×365×175 mm
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	2,4 kg
Shipping weight	3 kg

## Pictograms

### STANDARD



### OPTION

