



Robust laboratory and industrial precision scale for heavy items, verification optional

Features

- KERN PEJ: Automatic internal adjustment, guarantees high degree of accuracy and makes the balance independent of its location of use
- KERN PES: Adjusting program CAL for quick setting of the balance accuracy, external test weights at an additional price, see test weights
- Metal housing: robust and sturdy
- Weighing with tolerance range: a visual and audible signal helps with portioning, dispensing or grading
- Draught shield standard for models with weighing plate size **A**, weighing space W×D×H 170×150×100 mm
- **A**, **B** Underfloor weighing: load support with hook on the underside of the balance for models
- **A**, **B** Protective working cover included with delivery


Technical data

- Fluorescent display, bright with high contrast, digit height 14 mm
- Dimensions weighing surface, stainless steel
 - A** W×D 140×120 mm
 - B** W×D 200×200 mm, see larger picture
 - C** W×D 250×220 mm
- Overall dimensions (without draught shield) W×D×H
 - A**, **B** 220×333×93 mm
 - C** 260×330×113 mm
- Permissible ambient temperature 10 °C/30 °C


Accessories

- **A**, **B** Protective working cover, scope of delivery: 5 items, KERN PES-A04S05
- Relay output to connect relays, signal lamps, valves etc., 5 outputs for weighing in 3 tolerance ranges, must be ordered at purchase, KERN PES-A02
- Minimum weight of sample, depending on the required process accuracy, only in combination with a DAkkS calibration certificate, KERN 969-103
- Equipment qualification: compliant qualification concept with Installation and Operating Qualification (IQ, OQ), for details see page 232
- Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION



Model	Weighing capacity [Max]	Readability [d]	Verification value [e]	Minimal load [Min]	Linearity	Weighing plate	Net weight	Options	
								Verification	DAkkS Calibr. Certificate
KERN	g	g	g	g	g		kg	M KERN	DAkkS KERN
PES 620-3M	620	0,001	-	-	± 0,003	A	3,4	-	963-103
PES 2200-2M	2200	0,01	-	-	± 0,02	B	4,4	-	963-127
PES 4200-2M	4200	0,01	-	-	± 0,02	B	4,4	-	963-127
PES 6200-2M	6200	0,01	-	-	± 0,03	B	4,4	-	963-104
PES 15000-1M	15000	0,1	-	-	± 0,2	B	4,4	-	963-128
PES 31000-1M	31000	0,1	-	-	± 0,4	C	10	-	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

PEJ 620-3M	620	0,001	0,01	0,1	± 0,003	A	4,4	965-201	963-103
PEJ 4200-2M	4200	0,01	0,1	0,5	± 0,02	B	6	965-216	963-127
PEJ 2200-2M	2200	0,01	0,1	0,5	± 0,02	B	6	965-216	963-127