

# KERN PES 15000-1M

**KERN**

Robust laboratory and industrial precision scale for heavy items



## Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PES

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Tuning fork
Weighing capacity [Max]	15000 g
Readability [d]	0,1 g
Reproducibility	0,1 g
Linearity	± 0,2 g
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Resolution	150.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F1); 5 kg (F1)
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,3 g
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	g
Units	kg g ct

## Display

Display type	Fluorescent
Display backlight	LED is self-luminous

Display digit height	14 mm
Languages of the user interface	English

## Construction

Dimension housing (W×D×H)	220×333×93 mm
Dimensions weighing surface (W×D)	200×200 mm
Dimensions weighing surface	200×200 mm
Material housing	cast aluminium
Material weighing plate	stainless steel
Material platform	Stainless steel
Level indicator	✓
Levelling feet adjustable	✓

## Functions

Sum memory function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Underfloor weighing	Eye (included in delivery)
Capacity - Display	✓
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	150.000
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 30, 100
Auto-off interval(s) in mains power mode	free
Tare function	manual (multi)
Number of keys for operation	6

## Interface

Interfaces	RS-232 standard Digital I/O (optional, factory)
------------	--

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK

# KERN PES 15000-1M



Robust laboratory and industrial precision scale for heavy items

	US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100-240V AC; 0,6 A; 50/60Hz
Input voltage device / power [Max]	12 V, 1 A
Battery connection	Plug-in terminals

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Approval

CE mark	✓
---------	---

## Services (optional)


Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	330×440×215 mm
Shipping method	Parcel service
Net weight approx.	4,4 kg
Gross weight approx.	6 kg
Shipping weight	6,2 kg

## Pictograms

### STANDARD



### OPTION



### FACTORY

