

KERN PLS 720-3A

High-quality precision scale with comfortable graphic display and enormous weighing range



tl (Tw)
tl (HK)
ozt
tl (Singap, Malays)
ct
mo
lb
oz

Display

Display type	LCD graphic
Display backlight	✓
Display screen size	132×38 mm
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	210×340×120 mm
Dimensions completely mounted (W×D×H)	210×340×160 mm
Dimensions ring-shaped draught shield - inner (Ø×H)	150×60 mm
Dimensions ring-shaped draught shield - outer (Ø×H)	160×70 mm
Dimensions weighing surface (Ø)	110 mm
Dimensions weighing surface	110 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Material draught shield	glass
Level indicator	✓
Levelling feet adjustable	✓

Functions

Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Percentage determination	✓
Density determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Eye (included in delivery)

Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLS

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	720 g
Weighing capacity [Max] (ct)	3600 ct
Readability [d]	0,001 g
Readability carat [d] (ct)	0,01 ct
Reproducibility	0,001 g
Linearity	± 0,002 g
USP Minimum weight of sample (k = 2, U = 0.1%)	2 g
Resolution	720.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	600 g (E2)
Possible calibration points	100 g; 200 g; 300 g; 400 g; 500 g; 600 g
Stabilization time	2 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,005 g
Maximum creep (15 minutes)	10 mg
Maximum creep (30 minutes)	20 mg
Default unit	g
Units	g mg gn dwt

KERN PLS 720-3A



High-quality precision scale with comfortable graphic display and enormous weighing range

Function for averaging under unstable weighing conditions	✓
Time display	✓
Capacity - Display	✓
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	144.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	5 mg
Smallest piece weight when piece counting - normal conditions	50 mg
Reference quantity	10, 25, 50, 100, n (any number of pieces)
	off
Auto-off interval(s) in mains power mode	5 min 2 min 15 min
Tare function	manual (multi)
Number of keys for operation	6

Interface

Interfaces	RS-232 standard
EasyTouch (ET) - Connection type	über alle verfügbare Schnittstellen möglich

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	24 V; 1 A

Environmental conditions

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-103
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	500×360×420 mm
Shipping method	Parcel service
Net weight approx.	4,8 kg
Gross weight approx.	7 kg
Shipping weight	15,1 kg

Pictograms

STANDARD



OPTION

