

Product brochure

22.09.2026

KERN PWS 8000-1

High-resolution precision balance made of stainless steel with IP protection

ENGLISH



CONTACT

KERN & SOHN GmbH
Ziegelei 1
72336 Balingen
Germany

+49 7433 9933-0
info@kern-sohn.com
www.kern-sohn.com



FEATURES

- High-quality tuning fork weighing system for rapid display of the weight, very precise dispensing and a high level of mechanical robustness
- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- IP65 dust and spray protection (in accordance with EN 60529)
- CAL adjustment program for adjusting precision, external test weights available separately (see test weights)
- Level indicator and levelling feet for precise levelling of the scale, fitted as standard
- RS-232 data interface for connection to a printer as standard

TECHNICAL DATA

- Large LCD display, digit height 16,5 mm
- Dimensions weighing surface, stainless steel, W×D 190×190 mm
- Overall dimensions W×D×H 320×205×90 mm
- Net weight approx. 2,6 kg
- Permissible ambient temperature 5 °C/35 °C

MAIN SCOPE OF APPLICATIONS

- Environmental technology
- Water analysis
- Agricultural industry
- Cosmetics industry
- Food industry

PICTOGRAMS

Standard



Option



MODEL OVERVIEW

Model	Weighing capacity [Max]	Readability [d]	Reproducibility	Linearity	Dimensions weighing surface
PWS 8000-1	8200 g	0,1 g	0,1 g	± 0,2 g	190×190 mm

ACCESSORIES

Model	Description
EG-A07	Eyelet for underfloor weighing EG-A07
MLB-A05	RS232 interface cable MLB-A05
PWS-A01	Battery holder PWS-A01
PWS-A02	RS232 interface cable PWS-A02
YKC-01	Thermal printer YKC-01
YKG-01	Dot Matrix Printer YKG-01
YKH-01	Thermal printer YKH-01
YKI-02	RS232-Bluetooth-Adapter YKI-02
YKI-10	RS232-Ethernet adapter YKI-10 (RS-232 standard, Ethernet, RS-485)
YKI-11	RS232-Ethernet adapter YKI-11 (Ethernet, RS-232 standard - 2x)
YKI-12	RS232-WiFi adapter YKI-12
YKT-01	Needle printer YKT-01
YPS-03	Antivibration table YPS-03
YPS-04	Anti-vibration plate KERN YPS-04 (400×450×60 mm, 30 kg)
YPS-05	Anti-vibration plate KERN YPS-05 (565×450×60 mm, 42 kg)

ENGLISH

SOFTWARE

Model	Description
SCD-4.0-DL	Software SCD-4.0-DL (Scope of supplies: Download link for 1 license)
SCD-4.0-PRO-DL	Software SCD-4.0-PRO-DL (Scope of supplies: Download link for 1 license)
SCD-4.0-PRO-DL-AS05	Software SCD-4.0-PRO-DL-AS05 (Scope of supplies: Download link for 5 licenses)

SERVICES

Model	Description
963-128	DAkkS calibration certificate 963-128

Model	Description
969-517	Confirmation of the manufacturer's specification (only in combination with DAkkS calibration certificate)969-517
970-106	Warranty extension (+2 years) 970-106

KERN Pictogram Overview

	External adjustment: Adjusting accuracy using external adjustment weight
	Data interface RS-232: For connection to printers, PCs or other peripheral devices for data transfer over longer distances. Network in bus topology possible
	Piece counting: Reference quantities selectable. Display can be switched from piece to weight
	Density determination: The density of liquids and solids with a density of $\leq / \geq 1$ is determined directly in the measuring device
	Sum function: The weight values of weighed items can be added together and the total printed out
	Percentage determination: determining the deviation in % from the target value (100 %)
	Units can be switched to e.g. non-metric units
	Measuring with tolerance range (checkweighing): Upper and lower limit values can be programmed, e.g. for sorting, portioning or for measuring coatings or material thicknesses. The process is supported by an acoustic and/or optical signal
	Hold function: When the weighing conditions are unstable, a stable weight is calculated as an average value
	Protection against dust and water splashes IP65
	Universal plug-in power supply: With universal input and optional input socket adapters for EU, CH, GB or EU, CH, GB, US or EU, CH, GB, US, AUS
	Weighing principle tuning fork: A resonating body is electromagnetically excited, causing it to oscillate
	Package shipment by courier service: The duration of internal product provision is one day
	Suspended weighing: Load support with hook on the underside of the balance
	Battery operation: Ready for battery operation
	Accredited calibration (DKD): The duration of the accredited calibration is 3 working days