

KERN PWS 8000-1



High-resolution precision balance made of stainless steel with IP protection



Date of creation: 22.09.2026

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PWS
Measuring System	
Weighing system	Tuning fork
Number of weighing ranges	1
Weighing capacity [Max]	8200 g
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Readability [d]	0,1 g
Reproducibility	0,1 g
Linearity	± 0,2 g
Resolution	82.000
Tare range	8200 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	2 kg (F2); 5 kg (F2)
Stabilization time	3 s
Eccentric loading at 1/3 [Max]	0,5 g
Construction type of the scale	Single-range balance
Units	kg g gn dwt tl (Tw) tl (HK) ozt

	tl (Singap, Malays) ct lb oz tol mom
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	g

Display	
Display type	LCD
Display backlight	✓
Display screen size	109×27 mm
Display digit height	16,5 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	310×205×85 mm
Dimensions completely mounted (W×D×H)	320×205×90 mm
Dimensions weighing surface (W×D)	190×190 mm
Dimensions weighing surface	190×190 mm
Material housing	stainless steel
Material weighing plate	stainless steel
Material platform	stainless steel
Material substructure	plastic
Level indicator	✓
Levelling feet adjustable	✓

Functions	
PreTare function	✓
Sum memory function	✓
Percentage determination	✓
Density determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Eye (optional)
Function for averaging under unstable weighing conditions	✓
Capacity - Display	✓
Counting function	✓
Counting resolution (laboratory conditions)	82.000

KERN PWS 8000-1



High-resolution precision balance made of stainless steel with IP protection

Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Reference quantity	5, 10, 30, 100
IP protection - complete device	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Number of keys for operation	9

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Power supply cable removable	removable
Input voltage device / power [Max]	5,95 V, 1 A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 4,75 mm, Ø inside 1,7 mm, long 9,5 mm
Battery connection	Battery insert

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	408×315×220 mm
Shipping method	Parcel service
Net weight approx.	2,6 kg
Gross weight approx.	4,2 kg
Shipping weight	5,7 kg
Shipping volume weight	5,7 kg

Product information

GTIN/EAN number	4045761502994
Trade number	84238129
Warranty Time	36 mon
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

