



Stainless steel platform scales with IP65/67 protection, also with XL platform or optional verification

Features

- Ideal for the robust industrial applications
- Display device: stainless steel, protection against dust and water splashes IP65, (only when using rechargeable battery pack)
- Platform: made entirely of stainless steel, silicone-coated Stainless Steel load cell, protection against dust and water splashes IP67
- **1** KERN SFB-H: Column, standard, for models with weighing plate size
 - A** Height of stand approx. 200 mm
 - B** Height of stand approx. 400 mm

Technical data

- Large backlit LCD display, digit height 52 mm
- Dimensions of display device WxDxH 266x165x96 mm
- Weighing platform dimensions WxDxH, stainless steel
 - A** 300x240x107 mm **B** 400x300x111 mm
 - C** 500x400x120 mm **D** 650x500x139 mm
- Rechargeable battery pack integrated, as standard, operating time up to 35 h without backlight, charging time approx. 12 h
- Permissible ambient temperature -10 °C/40 °C

Accessories

- **2** KERN SFB: Stand, to be screwed onto the platform, height of stand approx. 600 mm, KERN SFB-A01
- Data interface RS-232, interface cable included, approx. 1,5 m, must be ordered at purchase, KERN KFN-A01
- Bluetooth data interface for wireless data transfer to PC or tablets, must be ordered at purchase, not in combination with verification, KERN KFB-A03
- Analogue module, must be ordered at purchase 0-10 V: KERN KFB-A04 4-20 mA: KERN KFB-A05
- Further details, plenty of further accessories and suitable printers see *Accessories*

*Please note: only one optional interface can be fitted for each device

STANDARD



OPTION



FACTORY



Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Weighing plate	Net weight approx. kg	Options		
							Verification	DAkkS	Calibr. Certificate
KERN							MET KERN	DAkkS KERN	
SFB 50K-3XL	50	5	-	-	C	14	-	-	963-128
SFB 100K-2XL	100	10	-	-	D	24	-	-	963-129
3 With elevated display									
SFB 10K1HIP	10	1	-	-	A	8	-	-	963-128
SFB 20K2HIP	20	2	-	-	A	8	-	-	963-128
SFB 50K5HIP	50	5	-	-	A	8	-	-	963-128
SFB 50K5LHIP	50	5	-	-	B	10	-	-	963-128
SFB 100K10HIP	100	10	-	-	B	10	-	-	963-129
Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.									
SFB 60K-2XLM	60	20	20	400	C	14	965-229	-	963-129
SFB 100K-2LM	150	50	50	1000	C	14	965-229	-	963-129
SFB 100K-2XLM	150	50	50	1000	D	24	965-229	-	963-129
3 With elevated display									
SFB 100K-2HM	150	50	50	1000	B	10	965-229	-	963-129
SFB 15K5HIPM	15	5	5	100	A	8	965-228	-	963-128
SFB 30K10HIPM	30	10	10	200	A	8	965-228	-	963-128
SFB 60K20LHIPM	60	20	20	400	B	10	965-229	-	963-129