

KERN SFB 50K5HIP

Stainless steel platform scale with IP65/IP67 protection and elevated display



Loadcell type	stainless steel IP67 silicone-coated
Load cell connection	6-wire

Display	
Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display segments	5 + 1/2
Display digit height	52 mm

Construction	
Dimensions completely mounted (W×D×H)	300×400×395 mm
Dimension display device (W×D×H)	266×165×96 mm
Dimensions weighing surface (W×D)	300×240 mm
Dimensions weighing surface	300×240 mm
Dimensions weighing platform (W×D×H)	300×240×105 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	stainless steel
Material load cell(s)	Stainless steels
Level indicator	✓
Levelling feet adjustable	✓
Stand height	200 mm
Stand inclinable	✓
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Cable length	0 m
Display device cable length	0 m
Allowed cable length display device [Max]	30 m

Functions	
Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Reference quantity	10, 20, 50, 100, 200
IP protection - display	IP65
IP protection - platform	no IP protection
IP protection - load cell	IP67

Category

Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SFB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	50 kg
Readability [d]	0,005 kg
Reproducibility	0,005 kg
Linearity	± 0,005 kg
Resolution	10.000
Tare range	-50 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (M1)
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,005 kg
Maximum creep (15 minutes)	20 g
Maximum creep (30 minutes)	40 g
Default unit	kg
Units	kg
	g
	lb
	Hj, tj
	lb:oz
Units (if device is conformity assessed)	kg

KERN SFB 50K5HIP

Stainless steel platform scale with IP65/IP67 protection and elevated display

Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
--	---

Auto-off interval(s) in mains power mode	off 5 min 30 min 15 min 3 min
--	---

Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
------------	---

EasyTouch (ET) - Compatibility	vollständig
--------------------------------	-------------

EasyTouch (ET) - Connection type	RS232 (+optionale Schnittstellen)
----------------------------------	-----------------------------------

Power Supply

Supplied power supply	Accu & Power supply
-----------------------	---------------------

Plug-in power supply type	Power adapter
---------------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
---	------------------------

Plug-in power supply / adapter for countries - optional	EURO UK US
---	------------------

Input voltage power supply / power [Max]	110 V - 230 V AC
--	------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Battery / accumulator type	Pb
----------------------------	----

Battery connection	Plug-in terminals
--------------------	-------------------

Rechargeable battery operating time - backlight on	20 h
--	------

Rechargeable battery operating time - backlight off	35 h
---	------

Rechargeable battery charging time	12 h
------------------------------------	------

Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	10 %
-------------------------------	------

Humidity of environment [Max]	95 %
-------------------------------	------

Storage temperature [Min]	-20 °C
---------------------------	--------

Storage temperature [Max]	60 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-248
---	---------

Article number for DAkkS calibration	963-128
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	695×415×225 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------


Net weight approx.	8 kg
--------------------	------

Gross weight approx.	10 kg
----------------------	-------

Shipping weight	13 kg
-----------------	-------

Pictograms

STANDARD



OPTION



FACTORY

