

SAUTER SV 100

KERN

Reliable luxmeter with large measuring range for versatile applications



Date of creation: 30.06.2026

Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Light measuring instrument
Product family	SV

Measuring System

Measuring range [Max] (Lux)	400000 lx
Readability illumination [d] (lx)	1 lx
Internal data memory: Number of value groups	99
Units	lx fc
Tolerance (% of [Max])	3%

Construction

Dimensions completely mounted (W×D×H)	235×65×40 mm
Material housing	plastic
Cable length	0,6 m

Functions

Hold function	✓
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	10 min

Power Supply

Supplied power supply	Battery
-----------------------	---------

Battery / accumulator type	Alkali(-Manganese)
Battery	3×1.5 V AAA
Battery connection	Pad + Spring
Battery operating time	100 h
Battery capacity	1.300 mAh
Battery voltage	4,5 V
Battery - Individual weight	11,5 g
Battery capacity (Wh)	1,95 Wh
Battery/Accu connected	not connected, enclosed

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-190
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	275×135×75 mm
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,30 kg
Shipping weight	0,6 kg
Shipping volume weight	0,6 kg

Product information

GTIN/EAN number	404576 1495616
Trade number	90278990
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

