

SAUTER TU 300-0.01US

Premium ultrasonic thickness gauge

KERN



Dimensions completely mounted (W×D×H)	132×76×32 mm
Material housing	cast aluminium
Cable length	0,9 m

Interface

Interfaces	USB-Device
------------	------------

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery operating time	100 h
Battery capacity	3.000 mAh
Battery voltage	1,5 V

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	60 °C
Storage temperature [Min]	-30 °C
Storage temperature [Max]	70 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-113
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	320×245×85 mm
Shipping method	Parcel service
Net weight approx.	0,55 kg
Gross weight approx.	1,8 kg
Shipping weight	1,638 kg

Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TU-US

Measuring System

Material thickness pulse-echo [Min] (mm)	3 mm
Material thickness pulse-echo [Max] (mm)	300 mm
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	14 mm
Measuring head measuring frequency	2,5 MHz
Units	mm inch
Internal data memory: Number of individual values	100
Internal data memory: Number of value groups	20
Tolerance (% of [Max])	0,5%

Display

Display type	LCD
--------------	-----

Construction

Dimension (W×D×H)	132×76×32 mm
Dimension housing (W×D×H)	132×76×32 mm

SAUTER TU 300-0.01US

Premium ultrasonic thickness gauge



Pictograms

STANDARD



OPTION

