

SAUTER TVL 500FHS71

The practical all-in-one package for rapid, simple testing



Type of drive	manual crank handle
Maximum clamp width	10 mm
Tensile/compressive force [Max]	500 N
Generated force [Max]	500 N
Traverse distance [Max]	230 mm

Functions

Function for averaging	✓
Limit-setting function	✓
Length measuring - zero setting	✓
Hold function	✓
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Power socket for mains adapter	Hollow plug, inside plus, outside 3,5 mm, inside 1,5 mm
Battery / accumulator type	NiMH
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Rechargeable battery charging time	4 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Category

Brand	Sauter
Product category	Force measurement
Product group	Force-Measuring Bundle
Product family	S71

Measuring System

Directions of force	tension compression
Measuring range force [Max] (N)	500 N
Readability force [d] (N)	0,1 N
Measuring head measuring frequency	2 kHz
Internal data memory: Number of value groups	1
Overload protection (% of [Max])	150%
Measurable length [Max]	20 cm
Tolerance (% of [Max])	0,5%
Internal data memory: Number of individual values	10
Default unit	N
Length measuring device	Length measuring device with display

Display

Display type	LCD
Display digit height	10 mm
Screen reversible	✓

Construction

Dimensions completely mounted (W×D×H)	230×66×36 mm
---------------------------------------	--------------

SAUTER TVL 500FHS71



The practical all-in-one package for rapid, simple testing

Services (optional)

Article number for DAkkS calibration (tensile force)	963-161
Article number for DAkkS calibration (compressive force)	963-261
Article number for DAkkS calibration (tensile force/ compressive force)	963-361
Article number for factory calibration (tensile force)	961-161
Article number for factory calibration (compressive force)	961-261
Article number for factory calibration (tensile force/ compressive force)	961-361

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	570×275×300 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	11 kg
Shipping weight	11 kg

Product information

GTIN/EAN number	4045761273641
Trade number	90248000
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

