

KERN PCB 300-2-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0



Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,03 g
Maximum creep (15 minutes)	40 mg
Maximum creep (30 minutes)	80 mg

Approval	
CE mark	✓

Display	
Display type	LCD
Display screen size	89×30 mm
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English Symbol language

Category	
Brand	KERN
Product category	Laboratory balances
Product group	Precision balances
Product family	PCB

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	300 g
Readability [d]	0,01 g
Resolution	30.000
Linearity	± 0,02 g
Reproducibility	0,01 g
Default unit	g

Units	kg
	g
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
	ffa
	m

Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 g (M1)
Possible calibration points	100 g; 200 g; 300 g
Stabilization time	3 s

Construction	
Dimension housing (W×D×H)	163×245×65 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (Ø)	105 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec

PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Underfloor weighing	Hook (included in delivery)

KERN PCB 300-2-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0

Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
IP protection - display	no IP protection

Counting	
Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, free, Input
Counting resolution (laboratory conditions)	15.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	6 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Battery	4×1.5 V AA
Battery / accumulator type	Li-Ion
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions	
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	235×365×175 mm
Net weight approx.	1,2 kg
Gross weight approx.	1,6 kg
Shipping weight	3 kg

Services (optional)	
Article number for DAkKS calibration	963-127
Article number for adjustment at the location of installation	961-247
Article number for certificate of conformity (verification)	969-517

Piktograms

STANDARD



OPTION

