

# KERN PLJ 720-3AM



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples



Minimum weight [Min]	0,02 g
USP Minimum weight of sample (k = 2, U = 0.1%)	2 g
Minimum weight [Min] (ct)	0,2 ct
Adjustment options	Internal calibration (automatic)
Automatic adjustment - Standard temperature deviation	1,2 °C
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,005 g

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	II
Verification scale interval [e]	0,01 g
Verification scale interval [e] (ct)	0,1 ct
Conformity assessment possible ex works	✓

Display	
Display type	LCD graphic
Display screen size	132×38 mm
Display backlight	✓
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction	
Dimension housing (W×D×H)	210×340×120 mm
Dimensions ring-shaped draught shield - inner (Ø×H)	150×60 mm
Dimensions ring-shaped draught shield - outer (Ø×H)	160×70 mm
Dimensions completely mounted (W×D×H)	210×340×160 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	110 mm
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLJ

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	720 g
Weighing capacity [Max] (ct)	3600 ct
Readability [d]	0,001 g
Readability carat [d] (ct)	0,01 ct
Resolution	720.000
Linearity	± 0,002 g
Reproducibility	0,001 g
Tare range	720 g
Default unit	g
Units	g mg gn dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz

Units (if device is conformity assessed)	g mg ct
--	---------------

# KERN PLJ 720-3AM



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples

Auto-off interval(s) in mains power mode	off 5 min 2 min 15 min
Capacity display	✓
Time display	✓
Tare function	manual (multi)
Density determination	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Sum memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard

## Counting

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	✓
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	720.000

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	24 V; 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK

	US CH EURO UK US CH
--	------------------------------------

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	500×360×420 mm
Net weight	4,9 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	15,1 kg

## Services (optional)

Article number for conformity assessment	965-216
Article number for DAkkS calibration	963-103
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION



### FACTORY

