



Discover more details and matching accessories online!

Professional model, counting resolution 60,000 points, verification optional

Features

- The automatic reference weight optimisation of reference weight gradually improves the average piece weight value
- Programmable using numerical key pad:
 - required reference quantity
 - known reference weight
- Three displays for weight display (verifiable), reference weight, total pieces
- Counting results memory: adds up all individual piece counts, result is shown in total weight and total pieces
- Fill-to-target function: Target count or target weight can be programmed. When the target value is reached, this will be indicated by an audible signal

- PRE-TARE function for manual subtraction of a known container weight, useful for checking fill-levels
- Thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations
- Changes from counting mode to weighing mode at the touch of a key
- Protective working cover included with delivery

Technical data

- Large backlit LCD displays, digit height 20 mm
- Dimensions weighing surface, stainless steel, WxD 295x225 mm
- Overall dimensions WxDxH 315x350x100 mm
- Net weight approx. 3,2 kg
- Permissible ambient temperature 0 °C/40 °C

Note: Official verification is mandatory for commercial trade

STANDARD										OPTION		FACTORY
											DAkkS	
												CPB-DM

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Smallest part weight (Normal) g/piece	Counting resolution Points	Options	
							Verification	Calibr. Certificate
KERN							KERN	DAkkS accr. KERN
CPB 6K0.1N	6	0,1	-	-	1	60.000	-	963-128
CPB 15K0.2N	15	0,2	-	-	2,5	60.000	-	963-128
CPB 30K0.5N	30	0,5	-	-	5	60.000	-	963-128
Multi-division balance, with increasing or decreasing load, it switches automatically to the next largest or smallest weighing range [Max] and readout [d].								
CPB 6K1DM	3 6	1 2	1 2	20	1	60.000	965-228	963-128
CPB 15K2DM	6 15	2 5	2 5	40	2,5	60.000	965-228	963-128
CPB 30K5DM	15 30	5 10	5 10	100	5	60.000	965-228	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.