

Counting scale KERN CXB · CXB-NM



**Note:** Official verification is mandatory for commercial trade.

Entry level model into professional counting, also with EC type approval [M], counting resolution of 30,000 points

**Features**

- Precise counting: The automatic reference weight optimisation of reference weight gradually improves the average piece weight value
- Programmable using numerical key pad:
  - required reference quantity
  - known reference weight
- Three displays for weight display, reference weight, total pieces
- Audible Fill-to-target: target quantity or target weight can be programmed, e. g. for checkweighing. When the target value is reached, a signal will sound
- 10 memories for reference weights
- Counting results memory: adds up all individual piece counts, result is shown in total weight and total pieces
- Energy management: Backlight turns off after 5 sec

- PRE-TARE function for manual subtraction of a known container weight, useful for checking fill-levels
- Two balances in one: Changes from counting mode to weighing mode at the touch of a key
- Protective working cover included with delivery
- Internal rechargeable battery pack included with the delivery

**Technical data**

- Large backlit LCD displays, digit height 18 mm
- Dimensions weighing surface, Stainless Steel, WxD 300x225 mm
- Dimensions housing WxDxH, 300x330x110 mm
- Internal rechargeable battery pack, operating time up to 200 h without backlight, charging time approx. 8 h
- Net weight approx. 4,0 kg
- Permissible ambient temperature -10 °C/40 °C

**Accessories**

- Protective working cover, scope of delivery: 5 items, KERN CXB-A01S05
- Internal rechargeable battery pack, operating time up to 200 h without backlight, charging time approx. 8 h, KERN GAB-A04

STANDARD

CAL EXT  
 PCS  
 SUM  
 ACCU  
 230 V  
 DMS  
 1 DAY

OPTION      FACTORY

DAkkS      M  
 +3 DAYS      +3 DAYS  
 CXB-NM

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Smallest part weight [Normal] g/piece	Counting resolution Points	Net weight approx. kg	Option					
								Verification		DAkkS Calibr. Certificate			
								KERN		DAkkS KERN			
<b>KERN</b>													
<b>CXB 3K0.2</b>	3	0,2	-	-	1	30.000	4,0	-			963-127		
<b>CXB 6K0.5</b>	6	0,5	-	-	2	30.000	4,0	-			963-128		
<b>CXB 15K1</b>	15	1	-	-	5	30.000	4,0	-			963-128		
<b>CXB 30K2</b>	30	2	-	-	10	30.000	4,2	-			963-128		
Note: For applications that require verification, please order verification at the same time, initial verification at a later date is not possible. Verification at the factory, we need to know the full address of the location of use.													
<b>CXB 3K1NM</b>	3	1	1	20	1	30.000	4,0	965-227			963-127		
<b>CXB 6K2NM</b>	6	2	2	40	2	30.000	4,2	965-228			963-128		
<b>CXB 15K5NM</b>	15	5	5	100	5	30.000	4,0	965-228			963-128		
<b>CXB 30K10NM</b>	30	10	10	200	10	30.000	4,2	965-228			963-128		

## Pictograms

<p><b>Internal adjusting:</b> Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)</p>	<p><b>KERN Communication Protocol (KCP):</b> It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems</p>	<p><b>Suspended weighing:</b> Load support with hook on the underside of the balance</p>
<p><b>Adjusting program CAL:</b> For quick setting up of the balance's accuracy. External adjusting weight required</p>	<p><b>GLP/ISO log:</b> The balance displays serial number, user ID, weight, date and time, regardless of a printer connection</p>	<p><b>Battery operation:</b> Ready for battery operation. The battery type is specified for each device</p>
<p><b>Easy Touch:</b> Suitable for the connection, data transmission and control through PC or tablet.</p>	<p><b>GLP/ISO log:</b> With weight, date and time. Only with KERN printers.</p>	<p><b>Rechargeable battery pack:</b> Rechargeable set</p>
<p><b>Memory:</b> Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.</p>	<p><b>Piece counting:</b> Reference quantities selectable. Display can be switched from piece to weight</p>	<p><b>Universal plug-in power supply:</b> with universal input and optional input socket adapters for A) EU, CH, GB; B) EU, CH, GB, USA; C) EU, CH, GB, USA, AUS</p>
<p><b>Alibi memory:</b> Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.</p>	<p><b>Recipe level A:</b> The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out</p>	<p><b>Plug-in power supply:</b> 230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available</p>
<p><b>Data interface RS-232:</b> To connect the balance to a printer, PC or network</p>	<p><b>Recipe level B:</b> Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display</p>	<p><b>Integrated power supply unit:</b> Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request</p>
<p><b>RS-485 data interface:</b> To connect the balance to a printer, PC or other peripherals. Suitable for datatransfer over large distances. Network in bus topology is possible</p>	<p><b>Totalising level A:</b> The weights of similar items can be added together and the total can be printed out</p>	<p><b>Weighing principle: Strain gauges:</b> Electrical resistor on an elastic deforming body</p>
<p><b>USB data interface:</b> To connect the balance to a printer, PC or other peripherals</p>	<p><b>Percentage determination:</b> Determining the deviation in % from the target value (100 %)</p>	<p><b>Weighing principle: Tuning fork:</b> A resonating body is electromagnetically excited, causing it to oscillate</p>
<p><b>Bluetooth* data interface:</b> To transfer data from the balance to a printer, PC or other peripherals</p>	<p><b>Weighing units:</b> Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details</p>	<p><b>Weighing principle: Electromagnetic force compensation:</b> Coil inside a permanent magnet. For the most accurate weighings</p>
<p><b>WiFi data interface:</b> To transfer data from the balance to a printer, PC or other peripherals</p>	<p><b>Weighing with tolerance range:</b> (Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model</p>	<p><b>Weighing principle: Single cell technology:</b> Advanced version of the force compensation principle with the highest level of precision</p>
<p><b>Control outputs (optocoupler, digital I/O):</b> To connect relays, signal lamps, valves, etc.</p>	<p><b>Hold function:</b> (Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value</p>	<p><b>Verification possible:</b> The time required for verification is specified in the pictogram</p>
<p><b>Analogue interface:</b> to connect a suitable peripheral device for analogue processing of the measurements</p>	<p><b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram.</p>	<p><b>DAKkS calibration possible (DKD):</b> The time required for DAKkS calibration is shown in days in the pictogram</p>
<p><b>Interface for second balance:</b> For direct connection of a second balance</p>	<p><b>Network interface:</b> For connecting the scale to an Ethernet network</p>	<p><b>Factory calibration (ISO):</b> The time required for Factory calibration is shown in days in the pictogram</p>
<p><b>Network interface:</b> For connecting the scale to an Ethernet network</p>	<p><b>Package shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram</p>	<p><b>Pallet shipment:</b> The time required for internal shipping preparations is shown in days in the pictogram</p>

\*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.

## KERN – Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAKkS calibration certificate the best pre-requisite for proper balance calibration.

The KERN DAKkS calibration laboratory today is one of the most modern and best-equipped DAKkS calibration laboratories for balances, test weights and force-measurement in Europe.

Thanks to the high level of automation, we can carry out DAKkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

### Range of services:

- DAKkS calibration of balances with a maximum load of up to 50 t
- DAKkS calibration of weights in the range of 1 mg - 2500 kg
- Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DAKkS calibration certificates in the following languages DE, EN, FR, IT, ES, NL, PL
- Conformity evaluation and reverification of balances and test weights

## Your KERN specialist dealer: