



Handy hanging scale for higher loads

Features

- **1** With the TÜV certification mark, the scales meet the requirements of the standard EN 13155 (Non-fixed load lifting attachments/ Breakage resistance) and EN 61010-1 (Electrical safety)
- Ideal for rapid control in goods-in and goods-out
- Also essential in the private sector to determine the weight of fish, game, fruits, bicycle parts, suitcases etc.
- Hold function: For easy reading of the weighing result, the display can be „frozen“ in different ways. Either automatically when the weighing value remains unchanged or manually by pressing the Hold key
- Peak load display (peak hold), Measuring frequency 5 Hz
- [Max] ≤ 200 kg: Snap link (stainless steel) with safety catch and hook (stainless steel) as standard, see larger picture

- **2** [Max] ≥ 500 kg: Reinforced version for heavy loads. Snap link and hook not included, see *Accessories*

Technical data

- LCD display, digit height 12 mm
- Hole diameter of load support, model with [Max] ≤ 200 kg: approx. 14 mm
- [Max] ≥ 500 kg: approx. 16 mm
- Weighing units: kg, lb, N
- Ready for use: Batteries included, 3×1.5 V AA, operating time up to 300 h
- Permissible ambient temperature 5 °C/35 °C

Accessories

Suitable for all models

- **3** Hook with safety catch, galvanised and lacquered cast steel, not rotatable, scope of delivery: 2 shackles, 1 connecting link, 1 hook, KERN YHA-06
- **4** High-strength shackle, hot-dipped galvanised cast steel bracket, curved edge. Scope of delivery: 2 shackles, KERN YSC-04

Suitable for all models with [Max] ≤ 200 kg

- Snap link (stainless steel) with safety catch, opening approx. 13 mm, KERN HCB-A01
- Hook (stainless steel), opening approx. 29 mm, KERN HCB-A02

Suitable for model HCB 20K10

- **5** Tare pan with pan beam, Max. load 30 kg, details see *Accessories*, KERN CH-A01N

STANDARD



OPTION



Model	Weighing capacity [Max] kg	Readability [d] g	Dimensions housing W×D×H mm	Net weight approx. kg	Options
					DAkks Calibr. Certificate DAkks KERN
HCB 20K10	20	10	82×43×153	0,30	963-128H
HCB 50K20	50	20	82×43×153	0,30	963-128H
HCB 99K50	99	50	82×43×153	0,30	963-129H
HCB 50K100	50	100	82×43×153	0,30	963-128H
HCB 200K100	200	100	82×43×153	0,30	963-129H
HCB 100K200	100	200	82×43×153	0,30	963-129H
HCB 200K500	200	500	82×43×153	0,30	963-129H
HCB 0.5T-3	500	1000	82×43×153	0,40	963-130H
HCB 1T-3	1000	2000	82×48×153	0,60	963-130H