



Discover more details and matching accessories online!

Highly versatile weighing beams (IP67) for large loads to 6 t

Features

- Flexible solution for weighing large, bulky or long items, thanks to freely positionable weighing beams and a 5 m (!) long connecting cable between the beams
- Thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations
- Weighing beams: steel, painted, 4 silicone-coated aluminium load cells, protection against dust and water splashes IP67
- **1** Sturdy handles for transporting the weighing beams
- **1** KERN UFA-L: Each weighing beam has a roller and handle for easy transport of the scale, see larger picture

- Display device: for details see KERN KFB-TM
- Benchtop stand incl. wall mount for display device as standard
- Totalising of weights and piece counts
- Protective working cover included with delivery
- KERN UFA-S: Model with short weighing beams, ideal for weighing compact items or animals in transport boxes
- Our floor scales are delivered in a robust wooden box. This protects the high-quality weighing technology from environmental influences and stresses during transportation

Technical data

- Large backlit LCD display, digit height 52 mm
- Dimensions of display device W×D×H 250×160×65 mm
- Cable length of display device approx. 5 m
- Cable length between weighing beams approx. 5 m
- Permissible ambient temperature -10 °C/40 °C

Shipment via freight forwarder. Please ask for dimensions, gross weight, shipping costs



Model	Weighing capacity [Max] kg	Readability [d] kg	Dimensions Weighing beam W×D×H mm	Net weight approx. kg	Options
					Calibr. Certificate DAkkS accr. KERN
KERN					
UFA 600K-1S	600	0,2	870×170×83	36	963-130
UFA 1.5T0.5	1500	0,5	1270×170×83	40	963-130
UFA 3T1	3000	1	1270×170×83	38	963-132
UFA 3T-3L	3000	1	2091×120×83	60	963-132
UFA 6T-3	6000	2	1270×160×115	90	963-132
UFA 6T-3L	6000	2	2091×160×115	130	963-132