

# KERN 572-32

All-rounder, e.g. as precision balance in the laboratory or in harsh industrial applications, ideal for the diverse possibilities of Industry 4.0 applications



	oz
	ffa
Maximum creep (15 minutes)	10 mg
Maximum creep (30 minutes)	20 mg
Default unit	g

Display	
Display type	LCD
Display type	7 segment LED
Display backlight	✓
Display screen size	89×30 mm
Display segments	7
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	180×310×85 mm
Dimensions completely mounted (W×D×H)	180×310×130 mm
Dimensions ring-shaped draught shield - inner (Ø×H)	157×43 mm
Dimensions ring-shaped draught shield - outer (Ø×H)	160×0 mm
Dimensions weighing surface (Ø)	106 mm
Dimensions weighing surface	106 mm
Material housing	cast aluminium
Material weighing plate	stainless steel
Material platform	stainless steel
Material draught shield	metal, lacquered
Level indicator	✓
Levelling feet adjustable	✓

Functions	
PreTare function	✓
Sum memory function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Eye (included in delivery)
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	420.000
Counting reference weight can be entered	✓

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	572

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	420 g
Readability [d]	0,001 g
Reproducibility	0,002 g
Linearity	± 0,005 g
Resolution	420.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 g (E2); 200 g (E2)
Possible calibration points	100 g; 200 g; 300 g; 400 g
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,005 g
USP Minimum weight of sample (k = 2, U = 0.1%)	4 g
Construction type of the scale	Single-range balance
Units	g gn dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb

# KERN 572-32



All-rounder, e.g. as precision balance in the laboratory or in harsh industrial applications, ideal for the diverse possibilities of Industry 4.0 applications

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Reference quantity	5, 10, 20, 50, free, Input
Hold function	✓
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

## Interface

Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
compatible with EasyTouch	✓

## Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Battery / accumulator type	Li-Ion
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h

Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional (factory)

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for DAkKS calibration	963-127
Article number for certificate of conformity	969-517

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	400×340×220 mm
Shipping method	Parcel service
Net weight approx.	2,4 kg
Gross weight approx.	3,8 kg
Shipping weight	6 kg

## Product information

GTIN/EAN number	4045761356849
REACH classification	no prohibited substances


# KERN 572-32



All-rounder, e.g. as precision balance in the laboratory or in harsh industrial applications, ideal for the diverse possibilities of Industry 4.0 applications

## Pictograms

### STANDARD



### OPTION



### FACTORY

