

KERN FH 2UK

Universal digital force gauge for tensile and compressive force measurements with integrated load cell, including UK adapter



Dimension display device (W×D×H)	230×66×36 mm
Material display housing	Plastics
Cable length	3 m
Load support (tensile force)	Hook

Functions

Function for averaging	✓
Limit-setting function	✓
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	UK

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
---	-------------------------------

Input voltage power supply / power [Max]	100 V - 240 V
--	---------------

Input voltage device / power [Max]	12 V, 400 mA
------------------------------------	--------------

Battery / accumulator type	NiMH
----------------------------	------

Rechargeable battery	8,4V / 1200mAh Ni-Hi
----------------------	----------------------

Rechargeable battery operating time - backlight on	10 h
--	------

Rechargeable battery operating time - backlight off	12 h
---	------

Rechargeable battery charging time	4 h
------------------------------------	-----

Environmental conditions

Ambient temperature [Min]	10 °C
---------------------------	-------

Ambient temperature [Max]	40 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (internal measuring cell)
Product family	FH-S

Measuring System

Measuring range force [Max] (N)	2 N
Readability force [d] (N)	0,001 N
Measuring head measuring frequency	2 kHz
Overload protection (% of [Max])	150%
Default unit	N
Internal data memory: Number of individual values	10
Internal data memory: Number of value groups	1
Number of platforms / channels	1
Tolerance (% of [Max])	0,5%
Directions of force	tension compression

Display

Display type	LCD
Display digit height	10 mm
Screen reversible	✓

Construction

Dimension housing (W×D×H)	230×66×36 mm
Dimensions completely mounted (W×D×H)	230×66×36 mm

KERN FH 2UK



Universal digital force gauge for tensile and compressive force measurements with integrated load cell, including UK adapter

Services (optional)

Article number for factory calibration (tensile force)	961-161
Article number for factory calibration (compressive force)	961-261
Article number for factory calibration (tensile force/ compressive force)	961-361

Packing & Shipping

Delivery time	1 d
Dimensions packaging (WxDxH)	312x170x60 mm
Net weight	0,62 kg
Shipping method	Parcel service
Net weight approx.	0,65 kg
Gross weight approx.	1,4 kg
Shipping weight	1,224 kg

Pictograms

STANDARD



OPTION

