

KERN HCB 100K200

KERN

Handy hanging scale for higher loads



Category

Brand	KERN
Product category	Industrial scale
Product group	Hanging scale
Product family	HCB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	100 kg
Readability [d]	0,2 kg
Reproducibility	0,2 kg
Linearity	± 0,4 kg
Resolution	500
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (M3)
Possible calibration points	50 kg
Stabilization time	2 s
Warm-up time	10 min
Maximum creep (15 minutes)	400 g
Maximum creep (30 minutes)	800 g
Eccentric/Off-centre loading is not possible	✓
Default unit	kg
Units	kg lb N
Internal measuring frequency	5 Hz
Tolerance (% of [Max])	0,5%
Loadcell type	aluminium
Load cell connection	4-wire

Display

Display type	LCD
Display backlight	no
Display digit height	12 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	82×43×153 mm
Dimensions housing - width (A)	82 mm
Dimensions housing - depth (B)	43 mm
Dimensions - total height/total length (D)	153 mm
Dimensions - inner length (E)	117 mm
Dimensions loop/top - hole diameter (F)	14 mm
Dimensions hook/bottom - hole diameter (G)	14 mm
Dimensions loop/top - thickness (H)	4 mm
Dimensions hook/bottom - thickness (I)	4 mm
Material housing	plastic
Material load hook	stainless steel
Material display housing	Plastics
Material load cell(s)	aluminium
Load cells - number	1

Functions

Function for averaging under unstable weighing conditions	✓
Hold function	✓
IP protection - load cell	no IP protection
Peak function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	off 4 min
Tare function	manual (multi)
Number of keys for operation	3

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	3×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	300 h
Battery voltage	4,5 V

KERN HCB 100K200



Handy hanging scale for higher loads

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Max]	60 °C

Approval

CE mark	✓
TÜV-tested	✓

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129H
Article number for certificate of conformity (verification)	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	215×150×85 mm
Net weight	0,262 kg
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,90 kg
Shipping weight	0,884 kg

Pictograms

STANDARD



OPTION

