

KERN OZL 464T24 1

The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OZL-S

Display

Display type	LCD touch
Display type	LCD touch
Display screen size	9,7"
Display resolution	2048×1536

Construction

Dimension (W×D×H)	300×240×640 mm
Optical system	Greenough
Tube type	Trinocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Light distribution	100:0
Contrasting methods	Bright field
Interpupillary distance [Min]	55 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
C-Mount magnification	0,5 x
C-Mount focusable	✓
Supported camera types	Microscope Camera

Functions

Camera - Applicable software	integrated
Supported operating systems	Android

Memory - total size	128 GB
---------------------	--------

Interface

Interfaces	WiFi standard USB 2.0 HDMI MicroSD card slot
------------	---

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	30 mm

Objective

Objectives magnifications	0,7 x - 4,5 x
---------------------------	---------------

Illumination

Illuminance	Reflected light Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination dimmable	Incident light + Transmitted light, separate

Focussing

Field of view [Min]	4,4 mm
Field of view [Max]	28,6 mm
Zoom [Min]	0,7 x
Zoom [Max]	4,5 x
Sample height [Max]	140 mm
Torque regulation	✓
Working distance	105 mm
Magnification ratio	6,4:1
Focusing mechanism	coarse drive

Stereomicroscope stand

Stand type	pillar
Diameter mounting microscope head (Ø)	76 mm

KERN OZL 464T24 1



The flexible, affordable all-rounder with zoom function as a digital solution for schools, training companies, inspection authorities and laboratories.

Camera

Cameratype	Tablet camera
Camera - Adapter type	C-Mount
Camera - Resolution	5 MP
Camera - Sensor type	Sony CMOS
Camera - Sensor size	1/2,8"
Camera - Colour depth	Colour
Camera - Framerate	30 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK
	US
	CH
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	590×440×390 mm
Net weight	5,075 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	7 kg
Shipping weight	20,2 kg

Pictograms