

KERN PCD 6K-4

High-resolution precision balance with removable display for maximum flexibility



mo
oz
ffa
tol

Display

Display type	LCD
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	165×280×75 mm
Dimensions device (W×D×H)	165×280×75 mm
Dimensions completely mounted (W×D×H)	165×280×75 mm
Dimension display device (W×D×H)	140×46×75 mm
Dimensions weighing surface (W×D)	160×160 mm
Dimensions weighing surface	160×160 mm
Dimensions weighing platform (W×D×H)	161×161×7 mm
Material housing	plastic
Material weighing plate	stainless steel
Material display housing	Plastics
Level indicator	✓
Levelling feet adjustable	✓
Stand height	250 mm
Stand inclinable	✓
Display device cable length	1,2 m

Functions

Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	5, 10, 20, 25, 50
Peak function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off

Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCD

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6000 g
Readability [d]	0,1 g
Reproducibility	0,1 g
Linearity	± 0,3 g
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Resolution	60.000
Tare range	6000 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (F1)
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,5 g
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g
Default unit	g

Units	g
	gn
	dwt
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct

KERN PCD 6K-4

KERN

High-resolution precision balance with removable display for maximum flexibility

Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 standard
EasyTouch (ET) - Connection type	RS232

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	US
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h
Rechargeable battery	PCD-A04
Rechargeable battery operating time - backlight on	12 h
Rechargeable battery operating time - backlight off	24 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	250×360×160 mm
Net weight	1,7 kg
Shipping method	Parcel service
Net weight approx.	1,8 kg
Gross weight approx.	2,2 kg
Shipping weight	2,9 kg

Pictograms

STANDARD



OPTION

