

# KERN TN 60-0.01EE

# KERN

Hand-held measuring device for ultrasonic material thickness testing in Echo-Echo principle



## Display

Display type	LCD
Display digit height	14 mm

## Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material housing	plastic
Cable length	0,9 m

## Functions

Memory function	✓
-----------------	---

## Interface

Interfaces	USB-Device
------------	------------

## Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery operating time	100 h
Battery capacity	3.000 mAh
Battery voltage	1,5 V

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for factory calibration	961-113
--	---------

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	320×250×85 mm
Net weight	0,29 kg
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	1,6 kg

## Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge Echo-Echo Method
Product family	TN-EE

## Measuring System

Material thickness echo-echo [Min] (mm)	3 mm
Material thickness echo-echo [Max] (mm)	60 mm
Material thickness pulse-echo [Min] (mm)	0,7 mm
Material thickness pulse-echo [Max] (mm)	600 mm
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	10 mm
Measuring head measuring frequency	5 MHz
Units	mm inch
Internal data memory: Number of individual values	100
Internal data memory: Number of value groups	20
Tolerance (% of [Max])	0,5%

# KERN TN 60-0.01EE




Hand-held measuring device for ultrasonic material thickness testing in Echo-Echo principle

Shipping weight 1,44 kg

## Pictograms

### STANDARD



### OPTION

