

# KERN UFA 6T-3

Highly versatile weighing beams (IP67) for large loads to 6000 kg



Display backlight	✓
Display segments	5 + 1/2
Display digit height	52 mm

## Construction

Dimension display device (W×D×H)	250×160×65 mm
Dimensions weighing surface (W×D)	1200×160 mm
Dimensions weighing surface	1200×160 mm
Dimensions weighing platform (W×D×H)	1270×160×115 mm
Material weighing plate	steel, lacquered
Material platform	steel, varnished
Material display housing	Plastics
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Stand inclinable	✓
Wall mount	✓
Cable length	3 m
Display device cable length	5 m
Allowed cable length display device [Max]	20 m
Load cells - number	4

## Functions

Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	None
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Reference quantity	10, 20, 50, 100, 200
IP protection - display	no IP protection
IP protection - load cell	IP67
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (multi)
Number of keys for operation	7

## Interface

Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V)
------------	---

## Category

Brand	KERN
Product category	Industrial scale
Product group	Weighing beam
Product family	UFA

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6000 kg
Readability [d]	2 kg
Reproducibility	2 kg
Linearity	± 4 kg
Resolution	3.000
Tare range	-6000 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6000 kg (M2)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	4 kg
Maximum creep (15 minutes)	8 kg
Maximum creep (30 minutes)	16 kg
Default unit	kg
Units	kg g lb oz lb:oz
Loadcell type	ZEMIC H8C 3 ton
Load cell connection	6-wire

## Display

Display type	LCD
--------------	-----


# KERN UFA 6T-3

Highly versatile weighing beams (IP67) for large loads to 6000 kg

Dimensions packaging (W×D×H)	1320×500×360 mm
Net weight	89 kg
Shipping method	Freight
Net weight approx.	90 kg
Gross weight approx.	115 kg
Shipping weight	112 kg

## Pictograms

### STANDARD



### OPTION



### FACTORY



	(optional, factory) analogue (4 - 20 mA) (optional, factory)
--	--

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
---	-------------------------------

Input voltage power supply / power [Max]	110 V - 230 V AC
--	------------------

Input voltage device / power [Max]	12 V, 500 mA
------------------------------------	--------------

Battery / accumulator type	Pb
----------------------------	----

Rechargeable battery	6 V, 1.2 Ah
----------------------	-------------

Rechargeable battery operating time - backlight on	8 h
--	-----

Rechargeable battery operating time - backlight off	35 h
---	------

Rechargeable battery charging time	10 h
------------------------------------	------

Rechargeable battery optional	Rchrg. battery optional (factory)
-------------------------------	-----------------------------------

## Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
---------------------------	-------

Humidity of environment [Min]	0 %
-------------------------------	-----

Humidity of environment [Max]	80 %
-------------------------------	------

## Approval

CE mark	✓
---------	---

## Services (optional)

Article number for adjustment at the location of installation	961-252
---	---------

Article number for DAkkS calibration	963-132
--------------------------------------	---------

Article number for certificate of conformity (verification)	969-517
---	---------

## Packing & Shipping

Delivery time	2 d
---------------	-----